

GUIDE

NEW FOR OLD – SIMPLY SWAP

DOMETIC ABSORPTION AND COMPRESSOR FRIDGES

 **DOMETIC**



NEW FOR OLD – SIMPLY SWAP
REFRIGERATORS

CONTENTS

Criteria to consider when swaping
the “old” refrigerator.

Absorption fridges 4 – 7

Compressor fridges 8 – 9

Campers and caravanners all over the world share the love for freedom and independence. Which is why most of them travel with ample stocks of food and drinks – well chilled of course for the best enjoyment. But what is the best way to keep travel provisions fresh and tasty? Dometic offers the widest choice of refrigerators for mobile use: silent absorption fridges and powerful compressor appliances with deep-freeze compartment, free-standing or nicely integrated in the kitchenette, many decors and designs, sizes and price categories, simple solutions and premium models as well equipped as your fridge at home.



**SPOILT FOR CHOICE?
HELP IS AT HAND...**



NEW FOR OLD – SIMPLY SWAP

Would you like to replace your good old absorption refrigerator with a contemporary one of the Dometic 10, 8 or 5 series to enjoy more convenience, up-to-date technology and a real eye-catcher in your kitchen?

Our swap guide helps you to find out which absorption or compressor refrigerator model best suits your size requirements.



VENTILATION CLEARANCE

Please note that the unit dimensions given in the tables on the next pages refer to the size of the refrigerator only. The size and position of the ventilation openings may differ from those of your current fridge. For Dometic refrigerators, a clearance of 15 mm to 25 mm must be maintained to the vehicle wall in addition to the depth dimension of the unit.



HEIGHT COMPENSATION

If your new Dometic refrigerator is a bit smaller in height than its predecessor, you can easily compensate for the height difference by attaching feet to the unit. For Thetford models, a minimum distance of 12 mm to the floor must be maintained if no feet are attached to the appliance.

Besides these general notes, it is always advisable to read the installation instructions of the desired appliance before replacing a refrigerator.

NEW FOR OLD – SIMPLY SWAP
ABSORPTION FRIDGES

ABSORPTION FRIDGES

↗ DOMETIC MODEL RM 300 P/A / RM 301 / RM 4290L RM 4300 / RM 6291 / RM 7290L RM 7291L / RMS 850x	↗ DOMETIC 	↗ DOMETIC MODEL RM 855x / RMS 855x	↗ DOMETIC 																				
THETFORD MODEL N3090A / N3090E / N4090A N4100A / N4100E+ / N90 1P N90 2E / N3097A / N3097E N4097A / N4097E	<table><tr><td>Model</td><td>RMS 10.5T</td></tr><tr><td>W x H x D (mm)</td><td>523 x 821 x 548 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>90 L</td></tr><tr><td>SKU</td><td>9600027101</td></tr></table>	Model	RMS 10.5T	W x H x D (mm)	523 x 821 x 548 (+15 up to 25)	Technology	Absorption	Volume	90 L	SKU	9600027101	THETFORD MODEL N3112A / N3112E / N4108A N4108E+ / N4112A / N112 1P N112 2E / N112 6E / N112 6A N3108E / N3108A / N97 1P N97 2E / N97 6E / N97 6A	<table><tr><td>Model</td><td>RMS 10.5XT</td></tr><tr><td>W x H x D (mm)</td><td>523 x 821 x 603 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>117 L</td></tr><tr><td>SKU</td><td>9600027116</td></tr></table>	Model	RMS 10.5XT	W x H x D (mm)	523 x 821 x 603 (+15 up to 25)	Technology	Absorption	Volume	117 L	SKU	9600027116
Model	RMS 10.5T																						
W x H x D (mm)	523 x 821 x 548 (+15 up to 25)																						
Technology	Absorption																						
Volume	90 L																						
SKU	9600027101																						
Model	RMS 10.5XT																						
W x H x D (mm)	523 x 821 x 603 (+15 up to 25)																						
Technology	Absorption																						
Volume	117 L																						
SKU	9600027116																						
↗ DOMETIC MODEL RM 400R / RM 400 P/C / RM 415 RM 4400xxx / RM 4401LM / RM 4405LM RM 6401 / RM 7401 L / RM 7405L RM 850x / RM5405LM / RM6400L / RM7400L	↗ DOMETIC 	↗ DOMETIC MODEL RML 8330 / RML 9330 / RML 9335 RML 9331 / RML 9430* / RML 9431* RML 9435*	↗ DOMETIC 																				
THETFORD MODEL N100 1P / N100 2E / N100 6E N100 6A / N3100A / N3104A N3100E / N3104A / N3104E N4100E+ / N4100A / N4104E+ N4104A / N104 1P / N104 2E N104 6E / N104 6A	<table><tr><td>Model</td><td>RM 10.5T</td></tr><tr><td>W x H x D (mm)</td><td>523 x 821 x 548 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>93 L</td></tr><tr><td>SKU</td><td>9600027098</td></tr></table>	Model	RM 10.5T	W x H x D (mm)	523 x 821 x 548 (+15 up to 25)	Technology	Absorption	Volume	93 L	SKU	9600027098	*Replacement Kit needed (9600025974).	<table><tr><td>Model</td><td>RML 10.4(T)</td></tr><tr><td>W x H x D (mm)</td><td>420 x 1293 x 578 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Absorption</td></tr><tr><td>Volume</td><td>133 L</td></tr><tr><td>SKU</td><td>9600027272</td></tr></table>	Model	RML 10.4(T)	W x H x D (mm)	420 x 1293 x 578 (+15 up to 25)	Technology	Absorption	Volume	133 L	SKU	9600027272
Model	RM 10.5T																						
W x H x D (mm)	523 x 821 x 548 (+15 up to 25)																						
Technology	Absorption																						
Volume	93 L																						
SKU	9600027098																						
Model	RML 10.4(T)																						
W x H x D (mm)	420 x 1293 x 578 (+15 up to 25)																						
Technology	Absorption																						
Volume	133 L																						
SKU	9600027272																						



↗ DOMETIC	↗ DOMETIC	↗ DOMETIC	↗ DOMETIC
MODEL		MODEL	
RM 4501 L / RM 4505 L / RM 7501 L RM 7505 L / RM 7601 L / RM 7605 L RMD 8501 / RMD 8505 /		RM 7801 L RM 7805 L / RM 7851 L+ / RM 7855 L RMD 8551 / RMD 8555 / RML 8550 RML 8551 / RML 8555	
THETFORD		THETFORD	
MODEL		MODEL	
N3145A / N3145E+ / N3150A N3150E / N4145E+ N4145A N4150E+ / N150 6E / N150 6A N145 6E / N145 6A		N4175E+ / / N4170E+ / N4170A N4175A / N3170E / N3170A N3175A / N3175E / N175 6E N175 6A	
Model	RMD 10.5(T)	Model	RMD 10.5X(T)
W x H x D (mm)	523 x 1245 x 550 (+15 up to 25)	W x H x D (mm)	523 x 1245 x 605 (+15 up to 25)
Technology	Absorption	Technology	Absorption
Volume	153 L	Volume	177 L
SKU	9600014843	SKU	9600027265
↗ DOMETIC	↗ DOMETIC	↗ DOMETIC	↗ DOMETIC
MODEL	No further replacement available!	MODEL	No further replacement available!
RM 200 / RM 2210 / RM 4200 RM 4210 / RM 4211 LM / RM5211LM / RM 5310		RM 270 / RM 2251 / RM 4230L / RM 5330	
Model		Model	
W x H x D (mm)		W x H x D (mm)	
Technology		Technology	
Volume		Volume	
SKU		SKU	



NEW FOR OLD – SIMPLY SWAP
ABSORPTION FRIDGES

COMPRESSOR FRIDGES

↗️ DOMETIC MODEL RM 275 / RM 4281 LM / RM 4261 / RM 5380 / RM 4280M / RM4285/ RMS8400 RM 4361 / RM4365LM/ RM 8400 / RM 2254 / RM 4360 L / RM 7360 L / RM 2253 / RM 4361 LM / RM 4365 LM RM 6361 L / RM 7361 L / RM 7365 L / RM 8401 ↗️ DOMETIC  <table><tr><td>Model</td><td>NRX 90V</td></tr><tr><td>W x H x D (mm)</td><td>486 x 821 x 480</td></tr><tr><td>Technology</td><td>Compressor</td></tr><tr><td>Volume</td><td>92 L</td></tr><tr><td>SKU</td><td>9620006673</td></tr></table>	Model	NRX 90V	W x H x D (mm)	486 x 821 x 480	Technology	Compressor	Volume	92 L	SKU	9620006673	↗️ DOMETIC MODEL RM 4270/ RM 6270/ RM7270L / RMS 8400 RMS 8401 ↗️ DOMETIC No further replacement available! <table><tr><td>Model</td><td></td></tr><tr><td>W x H x D (mm)</td><td></td></tr><tr><td>Technology</td><td></td></tr><tr><td>Volume</td><td></td></tr><tr><td>SKU</td><td></td></tr></table>	Model		W x H x D (mm)		Technology		Volume		SKU	
Model	NRX 90V																				
W x H x D (mm)	486 x 821 x 480																				
Technology	Compressor																				
Volume	92 L																				
SKU	9620006673																				
Model																					
W x H x D (mm)																					
Technology																					
Volume																					
SKU																					
↗️ DOMETIC MODEL RML 8230L ↗️ DOMETIC No further replacement available! <table><tr><td>Model</td><td></td></tr><tr><td>W x H x D (mm)</td><td></td></tr><tr><td>Technology</td><td></td></tr><tr><td>Volume</td><td></td></tr><tr><td>SKU</td><td></td></tr></table>	Model		W x H x D (mm)		Technology		Volume		SKU												
Model																					
W x H x D (mm)																					
Technology																					
Volume																					
SKU																					



ABSORPTION ADVANTAGE

NOISELESS COOLING WITH THREE ENERGY SOURCES

Absorption refrigerators run in silence, making them perfect for combined sleeping and cooking spaces. Plus, you can power them with mains, battery, and even LPG camping gas for flexible, reliable, virtually maintenance-free operation.

WHEN AN ABSORPTION REFRIGERATOR IS REPLACED WITH A COMPRESSOR UNIT, THE EXTERNAL VENTILATION GRIDS HAVE TO BE CLOSED.



Contents, specifications and availability are subject to change in the interests of technical improvement.

MOBILE LIVING MADE EASY — 7



NEW FOR OLD – SIMPLY SWAP
COMPRESSOR FRIDGES

COMPRESSOR FRIDGES

↗ DOMETIC MODEL RM 4501 L / RM 4505 L / RM 7501 L RM 7505 L / RM 7601 L / RM 7605 L RMD 8501 / RMD 8505	↗ DOMETIC  ModelRCD 10.5E W x H x D (mm)523 x 1282 x 565* (+15 up to 25) TechnologyCompressor Volume153 L SKU9600050528	↗ DOMETIC MODEL RM 7801 L / RM 7805 L / RM 7851 L+ RM 7855 L / RMD 8551 / RMD 8555 RML 8550 / RML 8551 / RML 8555	↗ DOMETIC  ModelRCD 10.5XE W x H x D (mm)523 x 1282 x 605* (+15 up to 25) TechnologyCompressor Volume177 L SKU9600050530
THETFORD MODEL N3145A / N3145E+ / N3150A N3150E / N4145E+ N4145A N4150E+ / N150 6E / N150 6A N145 6E / N145 6A / T2160		THETFORD MODEL N4145E / N4145A / N4150E+ N4175E+ / N4150A / N4170E+ N4170A / N4175A / T2175	
↗ DOMETIC MODEL RML 8330 / RML 9330 / RML 9331 RML 9335 / RML 9430* / RML 9431* RML 9435*	↗ DOMETIC  ModelRCL 10.4ET W x H x D (mm)420 x 1293 x 595 (+15 up to 25) TechnologyCompressor Volume151 L SKU9600049607	 💡 COMPRESSOR POWER COOLING AND DEEP-FREEZING UP TO -12 °C Compressor refrigerators offer outstanding energy efficiency and cooling performance even when ambient temperatures head for the extremes. They provide reliable cooling and deep-freezing down to -12 °C, even when operating on an angle. Suitable power sources: 12 V DC grid or solar panel.	

*Replacement Kit needed (9600025974).

*Due to the internal ventilation system, the RCD is 37 mm taller than the listed predecessor models.
If required the ventilation can be removed and replaced with ventilation slots in the furniture.



↗ DOMETIC MODEL -	↗ DOMETIC  <table><tr><td>Model</td><td>RC 10.4T 70</td></tr><tr><td>W x H x D (mm)</td><td>420 x 821 x 450 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Compressor</td></tr><tr><td>Volume</td><td>70 L</td></tr><tr><td>SKU</td><td>9600028399</td></tr></table>	Model	RC 10.4T 70	W x H x D (mm)	420 x 821 x 450 (+15 up to 25)	Technology	Compressor	Volume	70 L	SKU	9600028399	↗ DOMETIC MODEL -	↗ DOMETIC  <table><tr><td>Model</td><td>RC 10.4T 90</td></tr><tr><td>W x H x D (mm)</td><td>420 x 975 x 485 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Compressor</td></tr><tr><td>Volume</td><td>90 L</td></tr><tr><td>SKU</td><td>9600028400</td></tr></table>	Model	RC 10.4T 90	W x H x D (mm)	420 x 975 x 485 (+15 up to 25)	Technology	Compressor	Volume	90 L	SKU	9600028400
Model	RC 10.4T 70																						
W x H x D (mm)	420 x 821 x 450 (+15 up to 25)																						
Technology	Compressor																						
Volume	70 L																						
SKU	9600028399																						
Model	RC 10.4T 90																						
W x H x D (mm)	420 x 975 x 485 (+15 up to 25)																						
Technology	Compressor																						
Volume	90 L																						
SKU	9600028400																						
↗ THETFORD MODEL -		↗ THETFORD MODEL T1090 Floor level / T1090 Eye level T2090 Floor level / T2090 Eye level																					

↗ DOMETIC MODEL RM 300 P/A / RM 301 / RM 400 P/C RM 400R / RM 415 / RM 4290L / RM 4300 RM 4400 / RM 4401LM / RM 4405LM RM 6291 / RM 6401 / RM 7290L RM 7291L / RM 7401 L / RM 7405L RMS 850x / RM 850x	↗ DOMETIC  <table><tr><td>Model</td><td>RCS 10.5T</td></tr><tr><td>W x H x D (mm)</td><td>532 x 821 x 555 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Compressor</td></tr><tr><td>Volume</td><td>83 L</td></tr><tr><td>SKU</td><td>9600028196</td></tr></table>	Model	RCS 10.5T	W x H x D (mm)	532 x 821 x 555 (+15 up to 25)	Technology	Compressor	Volume	83 L	SKU	9600028196	↗ DOMETIC MODEL RM 855x / RMS 855x	↗ DOMETIC  <table><tr><td>Model</td><td>RCS 10.5XT</td></tr><tr><td>W x H x D (mm)</td><td>523 x 821 x 610 (+15 up to 25)</td></tr><tr><td>Technology</td><td>Compressor</td></tr><tr><td>Volume</td><td>98 L</td></tr><tr><td>SKU</td><td>9600028199</td></tr></table>	Model	RCS 10.5XT	W x H x D (mm)	523 x 821 x 610 (+15 up to 25)	Technology	Compressor	Volume	98 L	SKU	9600028199
Model	RCS 10.5T																						
W x H x D (mm)	532 x 821 x 555 (+15 up to 25)																						
Technology	Compressor																						
Volume	83 L																						
SKU	9600028196																						
Model	RCS 10.5XT																						
W x H x D (mm)	523 x 821 x 610 (+15 up to 25)																						
Technology	Compressor																						
Volume	98 L																						
SKU	9600028199																						
↗ THETFORD MODEL N3090A / N3090E / N4090A / N4100A- N4100E+ / N90 1P / N90 2E / N3097A N3097E / N4097A / N4097E / N100 1P N100 2E / N100 6E / N100 6A / N3100A- N3104A / N3100E / N3104A / N3104E N4100E+ / N4100A / N4104E+ N4104A / N104 1P / N104 2E N104 6E / N104 6A		↗ THETFORD MODEL N3112A / N3112E / N4108A N4108E+ / N4112A / N112 1P N112 2E / N112 6E / N112 6A N3108E / N3108A / N97 1P N97 2E / N97 6E / N97 6A																					




Dometic is a global company that makes mobile living easy – by providing great solutions to satisfy people's essential needs when they are on the move. Like cooking, taking care of personal hygiene and maintaining a pleasant temperature. We offer smart and reliable products with outstanding design.



Dometic on the web

Here's where you can find the complete Dometic range, with detailed information about all products. Plus, interesting facts about our company and download links for all of our catalogues.

dometic.com





THE FULL RANGE

View Products:

dometic.com

UNITED KINGDOM DOMETIC UK LTD.

Dometic House, The Brewery,
Blandford St. Mary
Dorset DT11 9LS

Tel 0344 626 0133

Fax 0344 626 0143

Mail sales@dometic.co.uk

GERMANY DOMETIC GERMANY GMBH

Hollefeldstraße 63
D-48282 Emsdetten

Tel +49 (0) 2572 879-0

Mail kontakt@dometic.de

